

Roll-out Trays

Construction Options and Modifications

APC -- All Plywood Construction
MI --- Matching Interior

- --- Available with an upcharge
- ☆ --- Available with exceptions
- (Blank) - Not available

 Look for the Harmony® storage solutions symbol

DROT	12	•24
code	width	depth

Material dimensions may be nominal based on lumber industry standards.

Specifications subject to change without notice.

Field Installation Chart


APC
MI

Cabinet	(Maximum)			
	#ROTs	#DROTs	#DXROTs	#HBRROTs
Base	5	3	3	2
Base•FH	7	4	4	3
Base•FH•40	7	5	5	3
Tall	10	10	10	5
Desk	3	2	2	1
Desk•FH	4	3	3	2
Vanity	5	3	3	2
Vanity•FH	7	4	4	3
VLC 88 1/2" H	6 (Top) 7 (Bottom)	6 (Top) 4 (Bottom)	6 (Top) 4 (Bottom)	3 (Top) 3 (Bottom)

Roll-out Trays Factory Installed

(price book pg. J5)

APC
MI



- * 1FWROT 1ROT
- * 2FWROT 2ROT
- * 3FWROT 3ROT
- * 4FWROT 4ROT
- * 5FWROT 5ROT
- * 6FWROT 6ROT


* When full-width Roll-out Trays (ROT) are ordered for 30", 33" or 36" wide cabinets, the double doors will have a mullion attached to the left door. Full width Roll-out Trays (ROT) are **not** available factory installed on Utility cabinets (U) wider than 24".

- 2 1/4" high tray has 1/2" thick solid wood sides and 3/16" Viraguard laminated plywood bottom
- 18", 21" and 24" depths only
- Shelves are eliminated when this option is selected
- Tray location is adjustable
- Full-width trays **not** available in 39", 42", 45" or 48"
- Trays are **not** evenly spaced
- Specify quantity
- Example:
Installed—U182484L-3ROT
Installed—B15L-3ROT
Installed—B36-3FWROT

Roll-out Trays Field Installation

(price book pg. J5)

APC
MI



- ROT12•24 •21 •18
- ROT15•24 •21 •18
- ROT16•24 •21 •18
- ROT18•24 •21 •18
- ROT19•24 •21 •18
- ROT21•24 •21 •18
- ROT22•24 •21 •18
- ROT24•24 •21 •18
- ROT27•24 •21 •18
- ROT30•24 •21 •18
- ROT33•24 •21 •18
- ROT36•24 •21 •18


- 2 1/4" high tray has 1/2" thick solid wood sides and 3/16" Viraguard laminated plywood bottom
- 18", 21" and 24" depths only
- Tray location is adjustable
- Mounting hardware and runners included
- Example:
For U182484—order ROT18•24
For B15L—order ROT15•24
For VB1518R—order ROT15•18
For VB15L—order ROT15•21



APC
MI

Deep Roll-out Trays Factory Installed

(price book pg. J5)



- * 1DFWROT
- * 2DFWROT
- * 3DFWROT
- * 4DFWROT
- * 5DFWROT
- * 6DFWROT

- 1DROT
- 2DROT
- 3DROT
- 4DROT
- 5DROT
- 6DROT

* When full-width Roll-out Trays (ROT) are ordered for 30", 33" or 36" wide cabinets, the double doors will have a mullion attached to the left door. Full width Roll-out Trays (ROT) are **not** available factory installed on Utility cabinets (U) wider than 24".


- 4" high tray has 1/2" thick solid wood sides and 3/16" Viraguard laminated plywood bottom
- 18", 21" and 24" depths only
- Shelves are eliminated when this option is selected
- Tray location is adjustable
- Full-width trays **not** available in 39", 42", 45" or 48"
- Trays are **not** evenly spaced
- Specify quantity
- Example:
Installed—U182484L-3DROT
Installed—B15L-2DROT
Installed—B36-2DFWROT



APC
MI

Deep Roll-out Trays Field Installation

(price book pg. J5)



- DROT12•24 •21 •18
- DROT15•24 •21 •18
- DROT16•24 •21 •18
- DROT18•24 •21 •18
- DROT19•24 •21 •18
- DROT21•24 •21 •18
- DROT22•24 •21 •18
- DROT24•24 •21 •18
- DROT27•24 •21 •18
- DROT30•24 •21 •18
- DROT33•24 •21 •18
- DROT36•24 •21 •18


- 4" high tray has 1/2" thick solid wood sides and 3/16" Viraguard laminated plywood bottom
- 18", 21" and 24" depths only
- Tray location is adjustable
- Mounting hardware and runners included
- Example:
For U182484—order DROT18•24
For B15L—order DROT15•24
For VB1518R—order DROT15•18
For VB15L—order DROT15•21



APC
MI

Deluxe Dovetailed Roll-out Tray Factory Installed

(price book pg. J5)



- * 1DXFWROT
- * 2DXFWROT
- * 3DXFWROT
- * 4DXFWROT
- * 5DXFWROT
- * 6DXFWROT

- ▲ 1DXROT
- ▲ 2DXROT
- ▲ 3DXROT
- ▲ 4DXROT
- ▲ 5DXROT
- ▲ 6DXROT

* When full-width Roll-out Trays (ROT) are ordered for 30", 33" or 36" wide cabinets, the double doors will have a mullion attached to the left door. Full width Roll-out Trays (ROT) are **not** available factory installed on Utility cabinets (U) wider than 24".


▲ **Not** available on double door cabinets with a center stile

- Roll-out Trays (ROT) are 4" deep, 3/4" solid wood dovetailed sides with 3/16" plywood bottom, notched front and full extension runners with integrated buffer
- 18", 21" and 24" depths only
- Shelves are eliminated when this option is selected
- Tray location is adjustable
- Full-width trays **not** available in 39", 42", 45" or 48"
- Trays are **not** evenly spaced
- Trays cannot be installed in the lowest position of a Knife Hinged cabinet. The hinge interferes with the tray's function.
- Example:
Installed—U182484L-3DXROT
Installed—B15L-2DXROT
Installed—B36-2DXFWROT

Available only in the width configurations shown

Deluxe Dovetailed Roll-out Tray Field Installation

(price book pg. J5)



- DXROT12•24 •21 •18**
- DXROT15•24 •21 •18**
- DXROT18•24 •21 •18**
- DXROT21•24 •21 •18**
- DXROT24•24 •21 •18**
- DXROT27•24 •21 •18**
- DXROT30•24 •21 •18**
- DXROT33•24 •21 •18**
- DXROT36•24 •21 •18**


- Roll-out Trays (ROT) are 4" deep, 3/4" solid wood dovetailed sides with 3/16" plywood bottom, notched front and full extension runners with integrated buffer
- 18", 21" and 24" depths only
- Tray location is adjustable
- Mounting hardware and runners included
- Trays cannot be installed in the lowest position of a Knife Hinged cabinet. The hinge interferes with the tray's function.
- Example:
For U182484—order DXROT18•24
For B15L—order DXROT15•24
For VB1518R—order DXROT15•18
For VB15L—order DXROT15•21



APC
MI

Roll-out Shelf Kit Field Installation

(price book pg. J5)



- ROSTK12•24•21•18**
- ROSTK15•24•21•18**
- ROSTK16•24•21•18**
- ROSTK18•24•21•18**
- ROSTK19•24•21•18**
- ROSTK21•24•21•18**
- ROSTK22•24•21•18**
- ROSTK24•24•21•18**
- ROSTK27•24•21•18**


- Field installation only
- Example:
For U182484—order ROSTK18•24
For B15L—order ROSTK15•24
For VB1518R—order ROSTK15•18
For VB15L—order ROSTK15•21
- Standard side-mount runners
- ☆ Must use MIP for Matching Interior Option



APC
MI

Base Cookware Storage Roll-out Field Installation

(price book pg. J6)



BCSRK24


- Fits into 24" wide 24" deep base or base full-height cabinets
- Satin nickel heavy duty wire rack
- Both shelves roll out independently of unit on full extension runners
- Shelf bottoms are birch veneer
- Top shelf is 11" x 21", bottom shelf is 12" x 21"
- Lower shelf has 9 1/2" clearance
- Side racks are 2 3/8" wide
- Field installation only



APC
MI

Base Pots and Pans Organizer Roll-out Field Installation

(price book pg. J6)



ROT30 •BPPSO

ROT36 •BPPSO

- 4" high Roll-out Tray with integrated shelf system
- Roll-out sides, back and shelves are 1/2" wood veneer plywood
- Mounting hardware and runners included
- 24" depth only
- Field installation only



APC
MI


High Back Roll-out Trays Factory Installed

(price book pg. J6)

- * 1HBFWROT
- * 2HBFWROT
- * 3HBFWROT
- * 4HBFWROT
- * 5HBFWROT

- 1HBROT
- 2HBROT
- 3HBROT
- 4HBROT
- 5HBROT

* When full-width Roll-out Trays (ROT) are ordered for 30", 33" or 36" wide cabinets, the double doors will have a mullion attached to the left door. Full width Roll-out Trays (ROT) are **not** available factory installed on Utility cabinets (U) wider than 24".




- 4" high tray has 7" high back, 1/2" thick solid wood front, back and sides and 3/16" Viraguard laminated plywood bottom
- 18", 21" and 24" depths only
- Shelves are eliminated when this option is selected
- Maximum of two can be installed vertically in a standard base cabinet
- Maximum of three can be installed vertically in a full-height door base cabinet
- Full-width trays **not** available in 39", 42", 45" or 48"
- Trays are **not** evenly spaced
- Specify quantity
- Example:
Installed—U182484L-3HBROT
Installed—B15L-2HBROT
Installed—B36-2HBFWROT

High Back Roll-out Trays Field Installation

(price book pg. J6)

- HBROT12•24 •21 •18
- HBROT15•24 •21 •18
- HBROT16•24 •21 •18
- HBROT18•24 •21 •18
- HBROT19•24 •21 •18
- HBROT21•24 •21 •18
- HBROT22•24 •21 •18
- HBROT24•24 •21 •18
- HBROT27•24 •21 •18
- HBROT30•24 •21 •18
- HBROT33•24 •21 •18
- HBROT36•24 •21 •18



- 4" high tray has 7" high back, 1/2" thick solid wood front, back and sides and 3/16" Viraguard laminated plywood bottom
- 18", 21" and 24" depths only
- Tray location is adjustable
- Mounting hardware and runners included
- Example:
For U182484—order HBROT18•24
For B15L—order HBROT15•24
For VB1518R—order HBROT15•18
For VB15L—order HBROT15•21


Roll-out Tray Divided Kit Field Installation

(price book pg. J6)

- | | |
|--------------------|----|
| ROTDK12•24 •21 •18 | 3 |
| ROTDK15•24 •21 •18 | 4 |
| ROTDK16•24 •21 •18 | 4 |
| ROTDK18•24 •21 •18 | 5 |
| ROTDK19•24 •21 •18 | 5 |
| ROTDK21•24 •21 •18 | 6 |
| ROTDK22•24 •21 •18 | 6 |
| ROTDK24•24 •21 •18 | 7 |
| ROTDK27•24 •21 •18 | 8 |
| ROTDK30•24 •21 •18 | 9 |
| ROTDK33•24 •21 •18 | 10 |
| ROTDK36•24 •21 •18 | 11 |

compartments

- Tray is 2 1/4" high at front and 10" high at back
- 18", 21" and 24" depths only
- Plywood doweled construction
- Example:
For B15L—order ROTDK 15•24
For B15R-RD18—order ROTDK 15•18





APC
MI


CD Roll-out Tray Factory Installed

(price book pg. J6)

1CDROT

2CDROT

- Black high density polypropylene material in a Deep Roll-out Tray (DROT)
- Maximum of two trays
- See field installed trays for capacity
- Only available on 15", 18", 21", 24", 30", 36", 42" and 48" wide cabinets
- Specify quantity
- Example:
Installed—U182484L-3CDROT
Installed—B15L-2CDROT
Installed—B36-2CDROT
- **Not** available in full-width cabinets over 24" wide



CD Roll-out Tray Field Installation

(price book pg. J6)



APC
MI

CDROT15-24 •21 •18

Capacity per section

14

CDROT18-24 •21 •18

19



CDROT21-24 •21 •18

23

CDROT24-24 •21 •18

28

- Black high density polypropylene material in a Deep Roll-out Tray (DROT)
- Allow 6" clearance above tray for full access



DVD Roll-out Tray Factory Installed

(price book pg. J6)


1DVDROT

2DVDROT

- Black high density polypropylene material in a Deep Roll-out Tray (DROT)
- Maximum of two trays
- See field installed trays for capacity
- Only available on 15", 18", 21", 24", 30", 36", 42" and 48" wide cabinets
- Specify quantity
- Example:
Installed—U182484L-3DVDROT
Installed—B15L-2DVDROT
Installed—B36-2DVDROT
- **Not** available in full-width cabinets over 24" wide



APC
MI



DVD Roll-out Tray Field Installation

(price book pg. J6)



APC
MI

DVDROT15-24 •21 •18

Capacity per section

11

DVDROT18-24 •21 •18

15



DVDROT21-24 •21 •18

19

DVDROT24-24 •21 •18

23

- Black high density polypropylene material in a Deep Roll-out Tray (DROT)
- Allow 6" clearance above tray for full access




CD/DVD Roll-out Tray Factory Installed

(price book pg. J6)

1CDDVDROT



2CDDVDROT

- Black high density polypropylene material in a Deep Roll-out Tray (DROT)
- Maximum of two trays
- See field installed trays for capacity
- Only available on 15", 18", 21", 24", 30", 36", 42" and 48" wide cabinets
- Specify quantity
- Example:
Installed—U182484L-3CDDVDROT
Installed—B15L-2CDDVDROT
Installed—B36-2CDDVDROT
- **Not** available in full-width cabinets over 24" wide




CD/DVD Roll-out Tray Field Installation


(price book pg. J6)



24" deep



21" deep



18" deep

Capacity per section
CD/DVD

CDDVDROT15-24 •21 •18	14/11
CDDVDROT18-24 •21 •18	19/15
CDDVDROT21-24 •21 •18	23/19
CDDVDROT24-24 •21 •18	28/23

- Black high density polypropylene material in a Deep Roll-out Tray (DROT)
- Allow 6" clearance above tray for full access